



# CI21 Transmitter

Low maintenance ammonia detection





GfGsafety.com/us-en

## CI21 Transmitter

#### Low maintenance ammonia detection

The charge carrier injection (CI21) sensor is a progressive development to improve upon current ammonia refrigeration detection methods. With CI21 technology sensor life is no longer limited to ammonia exposure levels. This reduces replacement costs associated with electrochemical sensors.

Charge carrier injection technology also eliminates false alarms frequently associated with metal oxide sensing (MOS). These, along with other features, provide reliable, cost effective, long-term safety.

The CI21 transmitter is an advanced development to which all other ammonia transmitters will be compared.

#### The new ammonia standard **Temperature influence**

Utilizing a controlled sensor voltage, the CI21 maintains a constant internal temperature, allowing accurate readings without additional heating components.

Graph 1 compares the temperature behaviors of metal oxide (MOS) and electrochemical sensors with the Cl21. The alarm threshold is set at 200 ppm, and each of the sensors is calibrated to 200 ppm NH3 at 77 °F. At lower temperatures, the response of the CI21 is extremely accurate, whereas the MOS and electrochemical sensors drift considerably.

If calibration is performed at lower temperatures, the identification shift to a higher ppm indication. As temperatures increase, the CI21 operates with the same reliability, whereas the MOS and electrochemical sensors indicate alarm conditions due to the higher slope of their indication lines.

#### **Humidity influence**


Fluctuating humidity levels are no longer an issue with the CI21. MOS sensors require a minimum humidity level in order to respond to leaks of ammonia, while the CI21 does not!

Low humidity is a typical condition of refrigerated areas due to lower temperatures. With the Cl21, a direct calibration with ammonia test gas can be accomplished with low humidity. As shown in graph 2, the influence of humidity on the CI21 is considerably less than MOS sensors.


#### **Sensor selectivity**


MOS sensors typically interfere with other gases and are rarely specific. Cross interferences occur with alcohol, cleaning detergents, water, carbon monoxide and many other substances. Interfering alarms become a nuisance that can lead to work stoppage and expensive shut downs. In graph 3, the cross-sensitivities of conventional sensors and the CI21 are plotted on a logarithmic axis.

GRAPH 1: Behavior of temperature after calibration with 200 ppm at 50 % r.M. (All sensors without temperature compensation)



220 GRAPH 2: Influence of humidity





## Technical Data: Cl21

Gas: Ammonia (NH3)

**Detection ranges: 20 - 200 ppm** 

30 - 1,000 ppm

30 - 10,000 ppm

Gas supply: Diffusion

**Expected sensor life:** Greater than 3 years

Temperature range: -40 to +131 °F / -40 to +55 °C Protection class: IP54 - Casing

Humidity: 0 to 99% r.h. non-condensing

Pressure: 90 to 110 kPa

Output signal: 0.2-1 mA or 4-20 mA Power supply: 10 to 30 V DC (300 mA

maximum)

Shielded cable: 3 wire x 18 AWG for

up to 500 yards

**Dimensions:** 3.9 x 3.9 x 2.2 in /

100 x 100 x 57 mm

(HxWxD)

Weight: 13.05 oz / 370 g **Approvals / Certifications:** 

c-CSA-us

CSA C22.2 No. 205-M1983

UL 916



### www.gfgsafety.com/us-en

© GfG Instrumentation, Inc. 2022 All specifications on this brochure are subject to technical changes due to further development.

USA and Canada Latin America Germany South Africa Asia Pacific Great Britain Switzerland France Poland Austria Netherlands

info@goodforgas.com info@goodforgas.com info@gfg-mbh.com info@gfg.co.za sales@gfg-asiapac.sg sales@gfggas.co.uk info@gfg.ch alainflachon@gfg-gasdetection.fr biuro@gfg.pl austria@gfg-mbh.com info@gfg-gasdetection.nl



GfG Instrumentation, Inc. 1194 Oak Valley Drive, Suite 20, Ann Arbor, MI 48108 USA Phone: (734) 769-0573 • Toll Free (USA / Canada): (800) 959-0329 Website: www.gfgsafety.com/us-en • info@goodforgas.com